Technical data sheet



Product:	58
Manufacturer:	H.B. FULLER
Product group:	KLEBSTOFF
Article group:	ANAEROB
Download:	12.05.2024

CYBERBOND SH 58

This data sheet was provided to you by Tewipack Uhl GmbH. The company tewipack Uhl GmbH assumes no responsibility for the topicality and the Accuracy of the information contained. The properties of the products can vary due to various influences such as composition and condition of the Substrate, impurities in or on the substrate, temperature and humidity at the Change storage and environmental conditions during use. Using this product in combination with other material, the customer is responsible for to check through our own tests whether the product is suitable for the planned combination and whether this combination delivers the expected results

Tewipack Uhl GmbH Industriestraße 15 D-75382 Althengstett

Telephone: E-Mail: +49(0)7051/9297-0 Fax Website: +49(0)7051/9297-99 www.tewipack.de

info@tewipack.de

Managing director: Alexander Uhl, Michael Uhl HRB 330424 Amtsgericht Stuttgart

Bank details: Sparkasse Pforzheim Calw BLZ 666 500 85 Konto 17 787 Commerzbank Sindelfingen BLZ 603 400 71 Konto 8 001 166

Vereinigte Volksbank AG Böblingen BLZ 603 900 00 Konto 80 089 003

Postbank Stuttgart BLZ 600 100 70 Konto 146 294 708



SH 58

Technical Datasheet

Profile:

Medium strength, very high viscosity, thixotropic Anaerobic curing sealant for flange and instant gasket applications with gap filling properties.

150

100


Shear rate

Physical properties - monomer

Base compound	Dimethacrylate
Appearance	Red
Gap filling capacity	0,10 - 0,50 mm
Fluorescent	Yes
Density at 20 °C	1,12 g/cm³
Shelf life at 20 °C in	
unopend bottles	12 months
Maximum thread	-

Adhesive strength

Substrate		Nm	
Steel	2	to	10
Stainless steel V2A	2	to	10
Galvanized steel	2	to	10
Brass	4	to	12



Breakloose torgue on M10 bolts and nuts in Nm according to DIN 54454, free swimming without ontorque.

Shear strength

Steel pin/collar 4 - 10 N/mm² specimen, after 24 h

Safety Information for Anaerobic Adhesives

Please consult the MSDS (Material Safety Data Sheet) before using. Keep the workplace clean and use in well ventilated areas only. Install suitable exhaust system at the workplace. Wear suitable safety glasses and gloves.

Viscositv

Cone / Plate,m	easured
at 20 °C	
@ 0.5 s-1	100.000 - 300.000 mPas
@ 160 s-1	19.000 - 28.000 mPas
200000 -	
ج ¹⁵⁰⁰⁰⁰ -	
. 100000 -	
	Cone / Plate,me at 20 °C @ 0.5 s-1 @ 160 s-1 200000 150000

50

Physical properties - Polymer

i hysical properties	i orynner
Full cure time [hours]	24
Appearance	Red
Temperature range	-50 - 150 °C

Setting time at 23 °C

50000

0

0

M10 brass bolt/nut 30 - 60

1

Solvent resistance	e	
Solvent alcohols	Example ethanol, methanol, isopropyl alcohol	Resistance +
esters	ethylacetate, benzoic benzyl ester	+
other liquids	water, freon, diesel oil	+
other liquids	ammonium hydroxide, bromine, chlorine, hydrobromic acid, lithium hydroxid, perchloric acid, potassium hydroxide	-
gases	acetylene, argon, butane, ethane, nitrogen	+
gases	ammonia, freon gas, oxygen (pure and /or oxygen rich systems)	-

General Information about Anaerobic Adhesives

Anaerobic adhesives and sealants cure by means of metal contact and/or due to the absence of air. Due to these facts they are only suitable for bonding and sealing metals. Therefore, as such they are not traditional adhesives as commonly known, but are specifically good for the bonding of metal cylindrical parts where torsion-load and shearing-load play an important part. Furthermore, anaerobics are excellent sealants for threads and flanges. Anaerobis are solvent free, one component adhesives. There are active metals (construction steel, tool steel, free cutting steel, brass, copper) and inactive metals (high alloyed or stainless steel, aluminium, electroplated surfaces, cast iron). While products used on active metals cure very fast, the same products need longer times to cure when used on inactive metals. But this does not influence the intended strength.

Storage

2

Store products in a cold and dark place. Optimal storage temperature range is between 8 °C - 21 °C.

Measurement of Viscosity

Viscosity describes the flow-ability of a liquid. Cyberbond measures the viscosity of the products by means of the cone/plate method: the liquid is applied on a panel and a defined cone presses the liquid together and rotates.

You differentiate between a Newtonian and a thixotropic liquid. In terms of a Newtonian liquid you will get a relative constant viscosity graph in dependence of the rotary speed of the cone. In terms of thixotropic liquids the product becomes more liquid (down to its base viscosity) the faster the cone rotates.

The viscosity is measured in mPa*s.

Clean Surface

The surface condition of the mating parts has an enormous influence on the success of a bond. To achieve good bonding success the mating parts should be clean. A certain amount of e.g. oil can be tolerated.

Additional Programme

In order to support certain applications Cyberbond offers perfectly balanced additional products such as: - Activator: in order to accelerate the curing of adhesives (Standard: CB 9191)

- Cleaner: in order to clean surfaces professionally (Standard: CB 9999)

LINOP Equipment

Cyberbond offers by means of the LINOP Equipment range suitable dosing and LED based curing devices. We also refer to suitable dosing tips which help an economical use of the adhesives (also if used manually).

The data mentioned in this TDS, particularly the recommendations and use of products are based on our recent knowledge and experience. Due to the fact of having so many different materials involved and conditions of applications which are out of our influence, we strongely recommend to do sufficient tests in order to guarantee that Cyberbond products are suitable for the intended process and applications. Exept for wilful acts any liability based on such recommendations or any verbal advice is hereby expressly exluded.

For safe handling information on this product, consult the Material Safety Data Sheet (MSDS).

Cyberbond Europe GmbH A H.B. Fuller Company Werner-von-Siemens-Straße 2 31515 Wunstorf Germany Tel.: +49 / 50 31 / 95 66 - 0 www.cyberbond.de



